

4


3

2

1


B

B




A

A



Transfer Tube




DETAIL A
SCALE 1 : 1

Brass Male Elbow
Hose 90 Degree
Connector

Note:

- When remote station is added , we remove the Bottle, Bottle Top, and Bottle Holder (check the details on 'ODOR CONTROL BOX' drawing) and replace it with Brass Male Elbow Hose 90° Connector
- In case of using two remote stations, we will use T-connector on the external Transfer Tube allowing single Odor Controller to drive both.



DETAIL B
SCALE 1 : 2

UNLESS OTHERWISE SPECIFIED:	NAME	DATE
DIMENSIONS ARE IN INCHES	DRAWN KASSIE	07/18/22
TOLERANCES:	CHECKED ENG'G	
FRACTIONAL ± 1/16	MFG APPR.	
ANGULAR: MACH ± 1° BEND ± 1°	PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CHUTES INTERNATIONAL MANUFACTURING. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF CHUTES INTERNATIONAL MANUFACTURING IS PROHIBITED.	
BEND-LINE PLACEMENT ± 0.010		
THREE PLACE DECIMAL ± 0.100		
WELD THICKNESS + 1/16		
SHEET METAL SPECIFICATIONS		
COMMENTS:		

CHUTES
PATENTED CHUTES INTERNATIONAL™

33 Industrial Park Dr.
Waldorf, MD 20602
Phone: (240) 448-5000
Fax: (301) 753-4108
WWW.CHUTES.COM

DESCRIPTION:
Remote Odor Control Assembly

SIZE B	PART ID: ODOR CONTROL	REV
DO NOT SCALE DRAWING	SCALE: 1:8	SHEET 1 OF 1